

13A - 250VAC Switched Recept. - Tamper Resistant Decora - With Integrated Double Pole Switchings Plus Ground

WARNINGS AND CAUTIONS:

- **TO AVOID FIRE, SHOCK, OR DEATH; TURN OFF POWER AT CIRCUIT BREAKER** or fuse and test that power is off before wiring!
- To be installed and/or used in accordance with appropriate electrical codes and regulations.
- If you are not sure about any part of these instructions, consult an electrician.
- Use this device with **copper or copper clad wire only**.
- To be installed with nema electrical boxes only.

INSTALLATION

1. **Turn power off.**
2. **Line & Neutral:** Remove insulation from each circuit conductor per strip gauge on device [approx. 1/2" (1.3 cm)]. Connect wires per wiring diagram as follows: Insert straight wires under clamps next to appropriate terminal screws. Tighten screw over wires with a force of 0.8 – 1.2 Nm (7 – 10.6 in-lbf) of torque.
NOTE: Terminal screws accept up to #12 AWG copper or copper clad wire.
3. **Ground:** Remove insulation from ground wire approx. 3/4" (1.9 cm). Connect wires per wiring diagram as follows: Loop wire clockwise 3/4 turn around ground screw. Tighten screw over wires with a force of 0.8 – 1.2 Nm (7 – 10.6 in-lbf) of torque.
NOTE: Ground screw accepts up to #12 AWG copper or copper clad wire.
4. Using the long mounting screws provided, mount device into a **nema outlet box**.
5. Mount wallplate and tighten cover screws.
6. Restore power at circuit breaker or fuse. **Installation is complete.**

NOTE: Meets IEC 60884-2-3 & SASO 2203

Wiring Diagram

