


SST Cat 6A U/UTP Euroclass Eca Cables

APPLICATION

Leviton SST Cat 6A U/UTP Cables exceed Cat 6A performance standards. They are rated to 500 MHz and are suitable for use in all Class E_A structured cabling systems. SST cables support 10 Gigabit Ethernet, Gigabit Ethernet, Power over Ethernet (PoE), voice, and broadband video transmissions at frequencies up to 500 MHz. SST offers unmatched assurance of network performance with superior signal isolation, excellent high-PoE performance, and best-in-class alien crosstalk performance. The specially designed isolation wrap construction provides superior heat management and noise-cancelling performance.



COUNTRY OF ORIGIN

UK

WARRANTY INFORMATION

For Leviton product warranties, go to [Leviton.com/ns/warranty](https://leviton.com/ns/warranty)

FEATURES & BENEFITS

- Small (6.9 mm) outer diameter
- Characterized to 550 MHz
- Exceeds PoE standards
- Assurance of network performance with superior signal isolation
- Guaranteed system margins when deployed with Leviton ATLAS-X1™ or EXTREME™ connectivity
- Designed and manufactured in Leviton's carbon neutral UK facility
- Reel packaging is 100% recyclable
- 23 AWG solid annealed copper wire
- 4 unshielded twisted pairs cabled together
- Central separator for increased internal crosstalk performance
- Isolation wrap construction delivers superior heat management and noise-cancelling performance without the need for grounding
- HFFR-LS (Halogen Free Flame Retardant – Low Smoke) jacket enables the cable to meet the requirements of the Construction Products Regulation (CPR) Euroclass Eca
- CE marked for CPR
- Supports 1 GbE with PoE up to 155 m when used in the ATLAS-X1™ SST MILLENNIUM™ System

STANDARDS & REGULATIONS

- ANSI/TIA 568.2-D
- ISO/IEC 11801 Class E_A and IEC 61156-5
- EN50173-1 and EN 50288-11-1
- IEEE 802.3 PoE Type 1, 2, 3, 4 (100 watts max)
- Cisco UPOE, UPOE+ (90 watts max)
- Power over HDBaseT™ PoH (95 watts max)

PRODUCT SPECIFICATIONS

SST Cat 6A U/UTP Euroclass Eca Cables

PRODUCT PERFORMANCE TRANSMISSION CHARACTERISTICS

Freq.	RL (dB)		NEXT (dB)		PS NEXT (dB)		IL (dB/100 m)	
	Standard	Typical	Standard	Typical	Standard	Typical	Standard	Typical
1	20.0	34.4	75.3	97.2	72.3	93.1	2.1	1.9
4	23.0	37.5	66.3	88.9	63.3	82.9	3.8	3.5
10	25.0	39.9	60.3	82.9	57.3	76.2	5.9	5.4
20	25.0	40.8	55.8	78.8	52.8	71.5	8.4	7.6
100	20.1	36.9	45.3	67.4	42.3	59.2	19.1	17.3
200	18.0	34.9	40.8	62.8	37.8	54.5	27.6	24.7
250	17.3	33.0	39.3	61.6	36.3	52.7	31.1	27.7
500	17.3	29.1	34.8	55.6	31.8	46.6	45.3	39.8
550	—	29.6	—	54.5	—	45.4	—	41.8

PRODUCT PERFORMANCE TRANSMISSION CHARACTERISTICS, CONTINUED

Freq.	ACRF (dB)		PSACRF (dB)		PSA NEXT (dB)		PSAACRF (dB)	
	Standard	Typical	Standard	Typical	Standard	Typical	Standard	Typical
1	68.0	97.4	65.0	95.8	67.0	94.0	67.0	91.6
4	56.0	90.8	53.0	85.2	67.0	93.9	66.2	90.6
10	48.0	83.0	45.0	77.3	67.0	105.1	58.2	102.7
20	42.0	77.3	39.0	70.8	67.0	104.8	52.2	101.6
100	28.0	63.6	25.0	56.1	62.5	104.1	38.2	89.7
200	22.0	56.9	19.0	49.8	58.0	92.9	32.2	67.1
250	20.0	55.8	17.0	49.2	56.5	91.5	30.2	64.0
500	14.0	48.3	11.0	42.7	52.0	90.5	24.2	51.3
550	—	47.1	—	40.7	—	85.1	—	46.8

- The standard values shown are the most demanding taken from the relevant IEC, TIA and EN specifications. These standard values are the maximum permissible for Insertion loss and the minimum permissible for other parameters
- N/A – Not Applicable

PRODUCT SPECIFICATIONS

SST Cat 6A U/UTP Euroclass Eca Cables

CHARACTERISTICS

Installation Characteristics

Min Bend Radius (Installation)	8 x Outer Diameter
Min Bend Radius (Operation)	4 x Outer Diameter
Field Test NVP Value	0.67
Temp. (Storage)	-20 °C to +75 °C
Temp. (Installation)	0 °C to +50 °C
Temp. (Operating)	-20 °C to +75 °C
Segregation Class	Class C

REACTION TO FIRE

Characteristic	IEC Standard	EN Standard	CPR Rating
Classification / EuroClass	—	EN 13501-6	Eca
Single Cable Flame Rating	IEC 60332-1-2	EN 60332-1-2	Pass

TECHNICAL SPECIFICATIONS

Primary Electrical Properties (20 °C)

CHARACTERISTIC	SPECIFICATION	TYPICAL PERFORMANCE
Conductor Loop Resistance	Max 19 Ω/100 m	16 Ω/100 m
Conductor Resistance Unbalance	Max 2%	0.1%
Insulation Resistance	>5G Ω.km	>50G Ω.km
Dielectric Strength	2500 Vdc/2secs	Pass

TECHNICAL SPECIFICATIONS

Secondary Electrical Properties (20 °C)

CHARACTERISTIC	SPECIFICATION	TYPICAL PERFORMANCE
Velocity of Propagation	<538 nsec/100 m @ 100 MHz	505 nsec/100 m @ 100 MHz
Delay Skew	Max 45 nsec/100 m @100 MHz	25 nsec/100 m @ 100 MHz
Characteristic Impedance (Fitted)	100 Ω +/- 5Ω @ 100 MHz	100 Ω ± 3 Ω @ 100 MHz

STANDARD PACKAGING SPECIFICATIONS – REELS

Part Number	Packaging Length (m)	Color	Nominal Cable Diameter (mm)	Nominal Cable Weight (kg/km)	Reel Size Flange Dia. x Width (mm)	Gross Weight (kg/Item)	Items Per Pallet
SST-Eca-500VT	500	Violet †	6.9	47	395 x 390	26.0	12
SST-Eca-305VT	305	Violet †	6.9	47	395 x 215	16.2	24
SST-Eca-500WH	500	White †	6.9	47	395 x 390	26.0	12
SST-Eca-305WH	305	White †	6.9	47	395 x 215	16.2	24
SST-Eca-500BU	500	Blue †	6.9	47	395 x 390	26.0	12
SST-Eca-305BU	305	Blue †	6.9	47	395 x 215	16.2	24

STANDARD PACKAGING SPECIFICATIONS – BOXES

Part Number	Packaging Length (m)	Color	Nominal Cable Diameter (mm)	Nominal Cable Weight (kg/km)	Box Size L x W x H (mm)	Gross Weight (kg/Item)	Items Per Pallet
SST-Eca-B305VT	305	Violet †	6.9	47	475 x 295 x 472	16.5	12
SST-Eca-B305WH	305	White †	6.9	47	475 x 295 x 472	16.5	12
SST-Eca-B305BU	305	Blue †	6.9	47	475 x 295 x 472	16.5	12

† Also available in a range of non-standard colors

For further support information, visit Leviton.com/ns/support