

Berk-Tek LANmark-A689 Cat 6 Solid CMR-CMX Outdoor PVC



Berk-Tek LANmark Industrial Light-Duty Ethernet Cables enable the expansion and integration of Ethernet into the Industrial environment. With over 50 years of manufacturing expertise, you can be sure these Industrial Cables will perform both mechanically and electrically. With its 600V AWM design, industrial PVC jacket, cold-bend performance, and resistance to sunlight and oil, this cable is suitable for light to medium duty, static, industrial applications. This Cat 6 compliant product offers best-in-class electrical performance including PSACR nearly 3 times better than the TIA specification and characterization up to 500 MHz, 300 MHz greater than the standard. It is rated CMR and CMX Outdoor, so it easily transitions from indoor to outdoor environments. It is also suitable for cable tray installations.

DESCRIPTION

Construction

23 AWG solid bare copper wire insulated with HDPE. Two insulated conductors twisted together to form a pair, Four such pairs and a cross filler form the basic unit, enclosed by polypropylene tape contained within an industrial PVC jacket.

Related Standards


Low Voltage - EU Directive 2014/35/EU, CE Approved

RoHS - EU Directive 2011/65/EU

PoE+ - Type 2 (802.3at)

Ratings		
Description	Method	
Listed Type	UL1666	CMR
Listed Type	UL444	CMX Outdoor
Oil Resistance	UL 1581 50.182	60°C
Sunlight Resistance	UL444 7.22	Yes (720 hrs)

Attributes		
Description	Method	
AWM Style	UL758	21695 (600V, 80°C)
Cold Bend	UL444 7.10	-40°C
Weld Spatter Resistance	Internal	Yes
Installation Pull Tension (Max):		
Bend Radius: > 3 inch	Internal	40 lbs.
Bend Radius: > 1.16 inch	TIA 568-C.0	25 lbs.
Abrasion	UL2556 7.10	75 cycles/1.5 lb. load



EtherNet/IP™
ODVA Compliant

STANDARDS

International ISO/IEC 11801;
ODVA EtherNet/IP Compliant

National ANSI/TIA-568.2-D;
UL 444

Berk-Tek LANmark-A689 Cat 6 Solid CMR-CMX Outdoor PVC



CHARACTERISTICS

Construction characteristics

Conductor material	23 AWG Solid Bare Copper
Filler	PVC filler
Insulation	HDPE
Jacket Material	PVC
Core Tape	Foamed polypropylene

Dimensional characteristics

Insulated conductor diameter (Nominal)	0.039 in
Average jacket thickness	0.03 in
Minimum jacket thickness at any point	0.024 in
Cable diameter (Nominal)	0.265 in
Nominal cable weight	30 lb/kft
Length per reel	1000.0 ft

Electrical characteristics

Mutual capacitance	5.6 nF/100m max.
DC Resistance (max.)	9.38 Ohm/100m
DC resistance unbalance (max.)	5 %
Nominal velocity of propagation	67 %



Transmission characteristics



Skew (max.)	45 ns/100m
-------------	------------

Usage characteristics

Minimum Bending Radius - Install	2.58 in
Recommended installation temperature range	-20 .. 80 °C
Recommended operating temperature range	-40 .. 80 °C
Recommended storage temperature range	-40 .. 80 °C

PRODUCT LIST

Part Number	Description	Packaging	Colour
 11099212	LANmark-A689 Cat 6 Solid CMR-CMX Outdoor PVC	Reel	Teal
 11101956	LANmark-A689 Cat 6 Solid CMR-CMX Outdoor PVC	Reel	Black

 = Make to order,  = In stock

Berk-Tek LANmark-A689 Cat 6 Solid CMR-CMX Outdoor PVC



LANMARK-A689 - TECHNICAL INFORMATION

Electrical Characteristics

FQ = Frequency (MHz) / TIA = TIA Spec / PG = Product Guarantee

	RL (dB)	NEXT (dB)	PSNEXT (dB)	ACRF (dB)	LCL/TCL
FQ	TIA / PG	TIA / PG	TIA / PG	TIA / PG	PG
1	20.00 / 20.00	74.30 / 79.30	72.30 / 77.30	67.80 / 72.80	50.00
4	23.00 / 23.60	65.30 / 70.30	63.30 / 68.30	55.80 / 60.70	44.00
10	25.00 / 26.00	59.30 / 64.30	57.30 / 62.30	47.80 / 52.80	40.00
16	25.00 / 26.00	56.20 / 61.30	54.20 / 59.30	43.70 / 48.70	38.00
20	25.00 / 26.00	54.80 / 59.80	41.80 / 57.80	41.80 / 46.80	37.00
31.25	23.60 / 25.00	51.90 / 56.90	49.90 / 54.90	37.90 / 42.90	35.10
62.5	21.50 / 23.50	47.40 / 52.40	45.40 / 50.40	31.90 / 36.80	32.00
100	20.10 / 22.50	44.30 / 49.30	42.30 / 47.30	27.80 / 32.80	30.00
150	18.90 / 21.60	41.70 / 46.70	39.70 / 44.70	24.30 / 29.30	28.20
200	18.00 / 21.00	39.80 / 44.80	37.80 / 42.80	21.80 / 26.70	27.00
250	17.30 / 20.50	38.30 / 43.30	36.30 / 41.30	19.80 / 24.80	26.00
300	— / 20.10	— / 42.10	— / 40.10	— / 23.30	25.20
350	— / 19.80	— / 41.20	— / 39.20	— / 21.90	24.60
400	— / 19.50*	— / 40.30*	— / 38.30*	— / 20.70*	24.00*
450	— / 19.20*	— / 39.50*	— / 37.50*	— / 19.70*	23.50*
500	— / 19.00*	— / 38.80*	— / 36.80*	— / 18.80*	23.00*
	IL (dB/100 m)	ACR (dB/100 m)	PSACR (dB/100 m)	PSACRF (dB/100 m)	EL TCTL
FQ	TIA / PG	TIA / PG	TIA / PG	TIA / PG	PG
1	2.00 / 2.00	72.20 / 77.30	70.30 / 75.30	64.80 / 69.80	35.00
4	3.80 / 3.80	61.50 / 66.60	59.50 / 64.50	52.80 / 57.70	23.00
10	6.00 / 5.90	53.40 / 58.40	51.30 / 56.40	44.80 / 49.80	15.00
16	7.60 / 7.50	48.80 / 53.80	46.70 / 51.70	40.70 / 45.70	10.90
20	8.50 / 8.40	46.40 / 51.40	44.30 / 49.40	38.80 / 43.80	9.00
31.25	10.70 / 10.60	41.40 / 46.40	39.20 / 44.30	37.90 / 39.90	—
62.50	15.40 / 15.30	32.40 / 37.10	30.00 / 35.10	28.90 / 33.80	—
100	19.80 / 19.70	25.20 / 29.70	22.50 / 27.60	24.80 / 29.80	—
150	24.70 / 24.50	16.90 / 22.20	14.90 / 20.20	21.30 / 26.30	—
200	29.00 / 28.80	10.80 / 16.00	8.80 / 14.00	18.80 / 23.70	—
250	32.80 / 32.60	7.30 / 10.80	3.50 / 8.70	16.80 / 21.80	—
300	— / 36.20	— / 6.00	— / 4.00	— / 20.30	—
350	— / 39.50	— / 1.70	— / —	13.90 / 18.90	—
400	— / 42.70*	— / -2.40*	— / —	12.80 / 17.70*	—
450	— / 45.70*	— / -6.20*	— / —	— / 16.70*	—
500	— / 48.60*	— / -9.80*	— / —	10.80 / 15.80*	—

*Values provided for reference only

Transmission Characteristics

Description

ISO/IEC 11801	Category 6
ANSI/TIA-568.2-D	Category 6
ODVA EtherNet/IP™ Compliant	Category 5e

Color Code

Pair-1	White/Blue	Blue
Pair-2	White/Orange	Orange
Pair-3	White/Green	Green
Pair-4	White/Brown	Brown

Copyright © 2020 Leviton Manufacturing Co., Inc. All rights reserved.
Leviton reserves the right to modify product specifications without notice.
SS2032-BTv1 - Released December 2020

Page 3 / 3

NETWORK SOLUTIONS HEADQUARTERS

Bothell, WA, USA | leviton.com/ns
(800) 824 3005 / +1 (425) 486 2222 | appeng@leviton.com

BERK-TEK A LEVITON COMPANY

New Holland, PA, USA | leviton.com/berktek
+1 (717) 354 6200 | berktek.support@leviton.com